ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

CPR4 1-1/4" Rigid Connector Threadless

Crouse-Hinds

Catalog Number	CPR4
Manufacturer	Crouse-Hinds
Description	Connector, 1-1/4 In Trade Size, CPR Model, Straight, Non-Insulated, 64 LB/100
Weight per unit	0.2200 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	2.0000 IN X 2.3800 IN X 2.3800 IN
Material	Malleable Iron

Dimensions and Weight

Size	1-1/4 in

Descriptions

Construction	Concrete Tight
Description	1-1/4" RIGID CONNECTOR THREADLESS
extra long description	MIDWEST CPR4 1 1/4 RGD CMP CONN
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea

Manufacturer Information

Brand	Eaton
GTIN	00784564122049
UPC	784564122049

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression Connector

Packaging

Carton	10
Weight Per each	0.22

Uses, Certifications, and Standards

standard	UL 514B, CUL