



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CR15I Duplex Recp 15A/125V Side Wire Iv

Pass & Seymour/Legrand

Catalog Number	CR15I
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Wire Ground Connection, Wall Mount, 1.322 In Length, 0.78 In Width, 3.281 In Height, Thermoplastic, Ivory, Impact Resistant, Corrosion Resistant, 0.2000 LB
Weight per unit	0.1956 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Wire Ground
indoor/outdoor	Indoor
media	Yes
Outlet Type	Indoor, Commercial
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wire Size	4

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	DUPLEX RECP 15A/125V SIDE WIRE IV
extra long description	P&S CR15I RECEP DUP 15A/125V SIDE W

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007119060
Manufacturers Part Number	CR15I
UPC	785007119060

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	100
Weight Per each	0.1956

Uses, Certifications, and Standards

Mounting	WALL
standard	CULUS, UL 498