



COMMERCIAL SPEC GRADE RECEPTACLE, SIDE WIRE, 20A, 125V, GRAY

CR20GRY | [Pass & Seymour](#)

FEATURES & BENEFITS

Commercial Spec Grade Duplex Receptacle, Side Wire 20amp 125volt, Gray



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Receptacles
Special Features: Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
cURus: No
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes

UN SPSC: 39121406

UR: No

DIMENSIONS

Depth (US): 0.78"

Height (US): 3.281"

Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





COMMERCIAL SPEC GRADE RECEPTACLE, SIDE WIRE, 20A, 125V, GRAY

CR20GRY | [Pass & Seymour](#)

FEATURES & BENEFITS

Commercial Spec Grade Duplex Receptacle, Side Wire 20amp 125volt, Gray



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Receptacles
Special Features: Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
cURus: No
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes

UN SPSC: 39121406

UR: No

DIMENSIONS

Depth (US): 0.78"

Height (US): 3.281"

Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

