



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



CR20GRY Duplex Recp 20A 125V Side Wire Gy

Pass & Seymour/Legrand

Catalog Number	CR20GRY
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Side Wire Connection, Wall Mount, 1.322 In Length, 0.78 In Width, 3.281 In Height, Thermoplastic, Gray, Impact Resistant, Corrosion Resistant, 0.2000 LB
Weight per unit	0.1962 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	DUPLEX RECP 20A 125V SIDE WIRE GY
extra long description	P&S CR20GRY RECEP DUP 20A/125V SIDE

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007119145
Manufacturers Part Number	CR20GRY
UPC	785007119145

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Packaging

Carton	1
Package	100
Weight Per each	0.1962

Uses, Certifications, and Standards

Mounting	WALL
Operating Temperature	-40°-60°C
standard	CULUS, UL 498