



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CR20LATR T-Res, Com GRD, 20A 125V, 5-20R, La, SW *Hubbell Wiring Devices*

Catalog Number	CR20LATR
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Tamper-Resistant Duplex Receptacle, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	8000
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

### Dimensions and Weight

Size	1.32 in x 1.14 in x 3.28 in
------	-----------------------------

### Descriptions

Description	T-RES, COM GRD, 20A 125V, 5-20R, LA, SW
extra long description	HWDK CR20LATR T-RES, COM GRD, 20A 1
Long Description	Straight Blade Tamper-Resistant Duplex Receptacle, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R
Product Type	T-Res, Com GRD, 20A 125V, 5-20R, La, SW
Special Features	Tamper Resistant

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585144313
Manufacturers Part Number	CR20LATR
series	Commercial Specification Grade
UPC	783585144313

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Tamper-Resistant



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186