



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS120GY Switch, Com, SP, 20A 120/277V, Gy *Hubbell Wiring Devices*

Catalog Number	CS120GY
Manufacturer	Hubbell Wiring Devices
Description	Toggle Switch, 1 Pole, 20 A, 120 to 277 V Ac, Thermoplastic (Body);Nylon (Toggle) Material, Steel Contact Material, Gray, Back and Side Wired Connection, Screw Mount, Zinc Plated (Bridge), 1.49 In (L) X 1 In (W) X 4.18 In (H), -40 °C Operating Temperature, +75 °C Operating Temperature, 0.15 LB
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Positive Snap
connection	Side Wired Only
Contact Configuration	Two Position
Contact Rating	Per UL 20
insulation	False
operating cycles	50,000
Switch Type	Toggle
Wattage	5540;5540.0000

Descriptions

Description	SWITCH, COM, SP, 20A 120/277V, GY
extra long description	HWDK CS120GY SWITCH, COM, SP, 20A 1

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585901213
UPC	783585901213

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
----------------------	---------------------

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount