



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS120I Switch, Com, SP, 20A 120/277V, Iv *Hubbell Wiring Devices*

Catalog Number	CS120I
Manufacturer	Hubbell Wiring Devices
Description	Toggle Switch, 1 Pole, 20 A, 120 to 277 V Ac, Double Pole Contact Configuration, Thermoplastic (Body);Nylon (Toggle) Material, Steel Contact Material, Ivory, Back and Side Wired Connection, Screw Mount, Zinc Plated (Bridge), 1.49 In (L) X 1 In (W) X 4.18 In (H), -40 °C Operating Temperature, +75 °C Operating Temperature, 0.15 LB
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Positive Snap
connection	Side Wired Only
Contact Rating	Per UL 20
insulation	False
operating cycles	50,000
Switch Type	Toggle
Wattage	5540;5540.0000

Descriptions

Description	SWITCH, COM, SP, 20A 120/277V, IV
extra long description	HWDK CS120I SWITCH, COM, SP, 20A 12

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585901152
UPC	783585901152

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
----------------------	---------------------

Packaging

Carton	10
Weight Per each	0.15

Uses, Certifications, and Standards

Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount