



## HARD USE SPECIFICATION GRADE SWITCH, WHITE

CSB20AC2W | [Pass & Seymour](#)

### FEATURES & BENEFITS

Construction 2pole Switch, Back & Side Wire, 20amp 120/277volt, White.



- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Duty: Hard Use

Number Of Poles: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 111

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

#### **DIMENSIONS**

Depth (US): 1.073"  
Height (US): 3.281"  
Width (US): 1.320"

#### **TECHNICAL INFORMATION**

Amps: 20A  
Volts: 120/277VAC  
Volts (AC): 120/277  
Grade Type: Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant





## HARD USE SPECIFICATION GRADE SWITCH, WHITE

CSB20AC2W | [Pass & Seymour](#)

### FEATURES & BENEFITS

Construction 2pole Switch, Back & Side Wire, 20amp 120/277volt, White.



- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Duty: Hard Use  
Number Of Poles: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes

UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

#### **DIMENSIONS**

Depth (US): 1.073"  
Height (US): 3.281"  
Width (US): 1.320"

#### **TECHNICAL INFORMATION**

Amps: 20A  
Volts: 120/277VAC  
Volts (AC): 120/277  
Grade Type: Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

