



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CS320BK Switch, Spec, 3W, 20A 120/277V, BK *Hubbell Wiring Devices*

Catalog Number	CS320BK
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Toggle Switch, Commercial Grade, Three Way, 20A 120/277V Ac, Side Wired, Black Toggle.
Weight per unit	0.0820 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SPDT
amperage rating	20
connection	Side Wired Only
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
Material	Nylon
operating cycles	50,000
pallet quantity	4050
Poles	Single Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540

### Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

### Descriptions

Description	SWITCH, SPEC, 3W, 20A 120/277V, BK
extra long description	HWDK CS320BK SWITCH, SPEC, 3W, 20A
Long Description	Switches and Lighting Controls, Toggle Switch, Commercial Grade, Three Way, 20A 120/277V AC, Side Wired, Black Toggle.
Product Type	Switch, Spec, 3W, 20A 120/277V, BK
Special Features	Standard Product

### Manufacturer Information

Brand	Hubbell Wiring Device-Kellems
GTIN	00783585189185
Manufacturers Part Number	CS320BK
series	General Purpose
UPC	783585189185



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE

## Packaging

Carton	1
Package	10
Weight Per each	0.082

## Uses, Certifications, and Standards

Application	Commercial Spec Grade
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed