

Eaton CSAS3F3CY1805

Catalog Number: CSAS3F3CY1805

Eaton Photoelectric Sensor Connector Cable, Global Plus, Accessory, Sensor connectivity, Micro-style straight female, AC, 3-wre, 18 AWG, 16.4 ft, 3 pin, PVC, 320V

General specifications



Product Name	Catalog Number
Eaton Global Plus connector cable	CSAS3F3CY1805
UPC	Product Length/Depth
782116143276	196.8 in
Product Height	Product Width
0.58 in	0.58 in
Product Weight	Warranty
0.7 lb	1 year
Certifications	
UL Listed	
CSA Certified	

defaultTaxonomyAttributeLabel

Type

Accessory

Cord length

196.8 ft

Operating Temperature

-13° to 176°F (-25° to 80°C)

Cable type

Polyvinyl Chloride (PVC)

Connection

Micro-style straight female

Number of wires

3

Wire size

#18 AWG

Environmental rating

IP67

Input voltage

320 V

Series

Global Plus

Switch type

Sensor connectivity

Power consumption

AC

Number of pins

3

Resources

Catalogs

[Volume 6: Solid-State Motor Control](#)

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - CSAS3F3CY1805](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)