



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSB120I Switch, Spec, SP, 20A 120/277V, B+S, Iv *Hubbell Wiring Devices*

Catalog Number	CSB120I
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Toggle Switch, Commercial Grade, Single Pole, 20A 120/277V Ac, Back and Side Wired, Ivory
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Positive Snap
amperage rating	20
connection	Back and Side Wired
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
Material	Nylon
operating cycles	50,000
pallet quantity	4500
Poles	Single Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540;5540.0000

Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

Descriptions

Description	SWITCH, SPEC, SP, 20A 120/277V, B+S, IV
extra long description	HWDK CSB120I SWITCH, SPEC, SP, 20A
Long Description	Switches and Lighting Controls, Toggle Switch, Commercial Grade, Single Pole, 20A 120/277V AC, Back and Side Wired, Ivory
Product Type	Switch, Spec, SP, 20A 120/277V, B+S, Iv
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585154046
Manufacturers Part Number	CSB120I
series	General Purpose
UPC	783585154046



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE

Packaging

Carton	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Commercial Spec Grade
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed