



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CSB20AC3W 20A 120/277VAC B+S Wire Comm 3W SW WH

*Pass & Seymour/Legrand*

Catalog Number	CSB20AC3W
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 2 Poles, 3 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, White, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.19 LB
Weight per unit	0.1893 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	4P
amperage rating	20
connection	Side Wire or external screw-pressure plate
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE COMM 3W SW W
extra long description	P&S CSB20AC3W 20A 120/277VAC B+S WI

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126297
Manufacturers Part Number	CSB20AC3W
UPC	785007126297



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	10
Package	50
Weight Per each	0.1893

## Uses, Certifications, and Standards

Mounting	WALL
standard	CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC