



## HARD USE SPECIFICATION GRADE SWITCH, IVORY

CSB20AC4I | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Construction 4way Switch, Back & Side Wire, 20amp 120/277volt, Ivory.

- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory

Duty: Hard Use

Number Of Poles: 4-way

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: 20

UL Standard: Yes

UN SPSC: 39121507

#### DIMENSIONS

Depth (US): 1.073"

Height (US): 3.281"

Width (US): 1.320"

**TECHNICAL INFORMATION**

Amps: 20A

Volts: 120/277VAC

Volts (AC): 120/277

Grade Type: Specification

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

