



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSB320STW 3W Tog, Com, ST, 20A 120/277V, WH Hubbell Wiring Devices

Catalog Number	CSB320STW
Manufacturer	Hubbell Wiring Devices
Description	Edgeconnect™, 3-Way Switch, Commercial Grade, Screwless Termination, Toggle, 20A 120/277V, White
Weight per unit	0.2000 (lbs/each)
Product Category	Wiring Devices

Features

action	Toggle
amperage rating	20
connection	Spring Termination
Contact Configuration	Two Position
Contact Rating	20A
insulation	#14 AWG min. - #10 AWG max. solid and stranded copper wire only
Material	Polycarbonate
operating cycles	100
Poles	3-way
Switch Type	Toggle
Voltage Rating	120/277

Descriptions

Description	3W TOG, COM, ST, 20A 120/277V, WH
extra long description	HWDK CSB320STW 3W TOG, COM, ST, 20A
Features	EdgeConnect™ Screwless Termination system, simply insert the wire and press the plunger down. No tools are required. That connection is fool-proof and long lasting, to all but guarantee a high quality result. Any qualified installer regardless of level of training can guarantee a high quality result. Elapsed time? About 11 seconds!
Long Description	EdgeConnect™, 3-Way Switch, Commercial Grade, Screwless Termination, Toggle, 20A 120/277V, White
Product Type	3W Tog, Com, ST, 20A 120/277V, WH
Special Features	Screwless Termination



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585964331
Manufacturers Part Number	CSB320STW
series	EdgeConnect™
UPC	783585964331

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	SWITCH

Packaging

Carton	1
Package	10
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Commercial
Enclosure	None
environmental conditions	UL 94V-2
Mounting	STRAP
standard	Fed Spec is W-S-896;NEMA® BI-WD and WD-6;UL20/CSA C22.2 No.111-18