

Eaton CSMS5D5CY1602

Catalog Number: CSMS5D5CY1602

Eaton Photoelectric Sensor Connector Cable, Global Plus, Accessory, Sensor connectivity, Mini-style straight female, AC/DC, 5-wire white/red/green/orange/black, 16 AWG, 6.6 ft, 5 pin, 8A, PVC, 600V

General specifications



Product Name	Catalog Number
Eaton Global Plus connector cable	CSMS5D5CY1602
UPC	Product Length/Depth
782116056743	78.72 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.47 lb	1 year
Certifications	
UL Listed	
CSA Certified	

defaultTaxonomyAttributeLabel

Type

Accessory

Amperage Rating

8A

Cord length

79.2 ft

Operating Temperature

-4° to 221°F (-20° to 105°C)

Cable type

Polyvinyl Chloride (PVC)

Connection

Mini-style straight female

Number of wires

5

White, red, green, orange, black

Wire size

#16 AWG

Environmental rating

NEMA 6P, IP68

Input voltage

600 V

Series

Global Plus

Switch type

Sensor connectivity

Power consumption

AC/DC

Number of pins

5

Resources

Catalogs

[Volume 6: Solid-State Motor Control](#)

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - CSMS5D5CY1602](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)