

# FEATURES

- · LED life-cycle of more than 10 years
- Quick installation
- Dual-voltage 120 or 277V AC input
- · Remote capacity or extended runtime option
- Damp Location Listed 20°C to 30°C (68°F to 86°F)
- · Fully adjustable, glare-free, lamp-heads
- · Provided with test switch and AC-On indicator
- · Wall or Ceiling mount



### **SPECIFICATIONS**

#### DESCRIPTION

- · The CU2 Series offers quality and value with a compact and attractive LED based emergency light
- The white or black housing and lamp-heads are made of high impact UL flame rated thermoplastic
- · Snap together design for quick and easy installation with option of Wall or Ceiling mount

**ORDERING GUIDE** 

 Remote capacity unit will run a double-head remote or 2 single-head remotes of either the Compass CIR or COR Series

#### DESCRIPTION

- · Also available with self-test/self-diagnostics to monitor battery/charger failure, battery disconnect and lamp failure
- Includes long-life Nickel Cadmium (NiCad) or Nickel Metal Hydride (NiMh) battery for UL recognized 90 minute emergency lighting
- · Remote Capacity(RC) models have a minimum runtime of 120 minutes when no remotes are installed

#### APPLICATION

• The CC SQ series can be applied in stair-wells, hallways, offices and commercial applications

#### LOCATION: DATE: PROJECT: TYPE: CATALOG #:

# tradeSELECT<sup>®</sup>



#### COMPLIANCES

- UL924 Listed for Damp Location
- NFPA 101 and NFPA 70
- OSHA
- CEC T20 Compliance

#### WARRANTY

· 2 year full unit warranty

Catalog Number			Accessories (Order Separately)	
CU2	White Finish, Dual-Head LED Emergency Light , 120/277 Input, NiCad Battery, 3 VDC, 1 Watt, CEC T20 Compliant	WGEL	6.25"H x	
CU2B	Black Finish, Dual-Head LED Emergency Light, 120/277 Input, NiCad Battery, 3 VDC, 1 Watt, CEC T20 Compliant	Wireguard	Wireguard 14"W × 4" D	
CU2RC	White Finish, Dual-Head LED Emergency Light, 120/277 Input, NiMh Battery, Remote Capacity, 3VDC, 1Watt	CIR Series	Matching LED Indoor	
CU2RCB	Black Finish, Dual-Head LED Emergency Light, 120/277 Input, NiMh Battery, Remote Capacity, 3VDC, 1Watt	_	Remote Heads	
CU2SD	White Finish, Dual-Head LED Emergency Light, 120/277VAC, NiCad Batt., 3 VDC, 1 Watt, Self-Test/Self-Diagnostics, CEC T20 Compliant	COR Series	Matching	
CU2RCSD	White Finish, Dual-Head LED Emergency Light, 120/277VAC, NiMh Batt. Remote Capacity, 3VDC, 1Watt, Self-Test/Self-Diagnostics	_	Outdoor Remote	
: Remote Capacity		Heads		

icity nly po

## **ENERGY CONSUMPTION**

	120 VAC	277 VAC
CU2	.56W	.54W
CU2RC	.92W	1.62W

#### currentlighting.com/compass

© 2022 HLI Solutions, Inc. All rights reserved. Information and specifications subject to change without notice. All values are design or typical values when measured under laboratory conditions.





LED EMERGENCY LIGHT

#### 

## DIMENSIONS

Master Carton Quantity








## APPLICATION INFORMATION

12 each



1 fc Average		
Path Width (PW)	Spacing (S)	
6'	16'	

Note: Meets Life Safety Code minimum illuminance of 0.1 fc and average illuminance of 1.0 fc. Assumes open space with no obstructions, ceiling height of 9' and reflectances of 80/50/20. Photometry files available on the website.