

DESCRIPTION

The CU2 Series offers quality and value with a compact and attractive LED based emergency light. The white or black housing and lamp-heads are made of high impact UL flame rated thermoplastic. Lamp-heads are fully adjustable and glare-free. Snap together design for quick and easy installation with option of Wall or Ceiling mount. Remote capacity unit will run a double-head remote or 2 single-head remotes of either the Compass CIR or COR Series. Also available with self-test/self-diagnostics to monitor battery/charger failure, battery disconnect and lamp failure.

FEATURES

- LED life-cycle of more than 10 years
- Quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium (NiCad) or Nickel Metal Hydride (NiMh) battery for UL recognized 90 minute emergency lighting
- Remote capacity or extended runtime option
- Damp Location Listed 20°C to 30°C (68°F to 86°F)
- Fully adjustable lamp-heads
- · Provided with test switch and AC-On indicator
- Wall or Ceiling mount
- Remote Capacity(RC) models have a minimum runtime of 120 minutes when no remotes are installed



APPLICATION

The CU2 Series can be applied in stair-wells, hallways, offices and other commercial applications.

STANDARDS, CERTIFICATION, AND COMPLIANCE

UL924 Listed for Damp Location NFPA 101 and NFPA 70 OSHA CEC T20 Compliance

WARRANTY

2 year full unit warranty

SELF-DIAGNOSTIC FEATURES


- Fault identification for battery, charger, LED integral lamps and remotes
- Self-Testing monthly and annual for 90 minutes
- Manual testing for 30 second, 15 minute and 90 minutesWall or Ceiling mount


ORDERING GUIDE

Catalog Number	Description
CU2	White Finish, Dual-Head LED Emergency Light , 120/277 Input, NiCad Battery, 3 VDC, 1 Watt, CEC T20 Compliant
CU2B	Black Finish, Dual-Head LED Emergancy Light, 120/277 Input, NiCad Battery, 3 VDC, 1 Watt, CEC T20 Compliant
CU2RC	White Finish, Dual-Head LED Emergency Light, 120/277 Input, NiMh Battery, Remote Capacity, 3VDC, 1Watt
CU2RCB	Black Finish, Dual-Head LED Emergency Light, 120/277 Input, NiMh Battery, Remote Capacity, 3VDC, 1Watt
CU2SD	White Finish, Dual-Head LED Emergency Light, 120/277VAC, NiCad Batt., 3 VDC, 1 Watt, Self-Test/Self-Diagnostics, CEC T20 Compliant
CU2RCSD	White Finish, Dual-Head LED Emergency Light, 120/277VAC, NiMh Batt. Remote Capacity, 3VDC, 1Watt, Self-Test/Self-Diagnostics

Note: Remote Capacity Unit will only power the Compass Indoor and Outdoor Remote(CIR and COR Series)

DIMENSIONS





Single Carton Weight: 1 lbs.

Master Carton Quantity: 12 each

ENERGY CONSUMPTION

	120 VAC	277 VAC
CU2	.56 W	.54 W
CU2RC	.92 W	1.62 W

ACCESSORIES

WGLZ Wireguard - 6.25" H X 14" W X 4" D CIR Series - Matching LED Indoor Remote Heads COR Series - Matching LED Outdoor Remote Heads









S CORD CIRD

D CORS