

DESCRIPTION

The CU2SO provides 90 minutes of emergency lighting in the event of power outage. The CU2SO offers quality and value with a compact and attractive LED based emergency light. The white housing is made of high impact UL flame rated thermoplastic, and clear cover is made of impact resistant polycarbonate. The fully gasketed and shielded housing protects the unit from wind driven rain. Snap together design for quick and easy installation with option of wall or ceiling mount.



APPLICATION

The CU2SO can be applied in areas susceptible to rain and severe moisture. Some of these include outside over doors, in parking garages, around pools or in basements.

STANDARDS, CERTIFICATION, AND COMPLIANCE

UL924 Listed for Wet Location
 NFPA101 and NFPA70
 OSHA

WARRANTY

2 year full unit warranty

FEATURES

- LED Life-cycle of more than 10 years
- Quick Installation
- Dual-Voltage 102/277VAC Input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Wet Location Listed 0°C to 40°C (32°F to 104°F)
- Fully Adjustable lamp-heads
- Includes test switch and AC-On indicator


ENERGY CONSUMPTION

	120 VAC	277 VAC
CU2SO	3.59 W	3.40 W

ORDERING GUIDE

Catalog Number	Description
CU2SO	Clear poly-carbonate shield with White Thermoplastic Housing, Dual LED Lamps, UL Wet Location Listed, 120/277VAC Input,, 3.6VDC, 1.36W per lamp-head, 99 lumens per head

DIMENSIONS



Single Carton Weight: 3 lbs.
 Master Carton Quantity: 12 each

DESCRIPTION

The CU2SO provides 90 minutes of emergency lighting in the event of power outage. The CU2SO offers quality and value with a compact and attractive LED based emergency light. The white housing is made of high impact UL flame rated thermoplastic, and clear cover is made of impact resistant polycarbonate. The fully gasketed and shielded housing protects the unit from wind driven rain. Snap together design for quick and easy installation with option of wall or ceiling mount.



APPLICATION

The CU2SO can be applied in areas susceptible to rain and severe moisture. Some of these include outside over doors, in parking garages, around pools or in basements.

STANDARDS, CERTIFICATION, AND COMPLIANCE

UL924 Listed for Wet Location
 NFPA101 and NFPA70
 OSHA

WARRANTY

2 year full unit warranty

FEATURES

- LED Life-cycle of more than 10 years
- Quick Installation
- Dual-Voltage 120/277VAC Input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Wet Location Listed 0°C to 40°C (32°F to 104°F)
- Fully Adjustable lamp-heads
- Includes test switch and AC-On indicator


ENERGY CONSUMPTION

	120 VAC	277 VAC
CU2SO	3.59 W	3.40 W

ORDERING GUIDE

Catalog Number	Description
CU2SO	Clear poly-carbonate shield with White Thermoplastic Housing, Dual LED Lamps, UL Wet Location Listed, 120/277VAC Input,, 3.6VDC, 1.36W per lamp-head, 99 lumens per head

DIMENSIONS



Single Carton Weight: 3 lbs.
 Master Carton Quantity: 12 each