



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CVS2100XMM CVS 2P 100AS 42KA 240 Vac Load Terms W/Hardware

Eaton Corp

Catalog Number	CVS2100XMM
Manufacturer	Eaton Corp
Description	Eaton Type CV Molded Case Circuit Breaker, Molded Case Circuit Breaker, 100 A, 42 Kaic, Two-Pole, #6 - 4/0 Al/Cu, CV, #4/0 Kcmil Maximum Load, Includes Mounting Kit
Weight per unit	4.0 (lbs/each)
Product Category	2 Pole

Features

Current Rating	100 A
dimensions	7.5000 IN X 3.5000 IN X 5.0000 IN
Poles	2

Descriptions

Description	CVS 2P 100AS 42KA 240 VAC LOAD TERMS W/HARDWARE
extra long description	ETN CVS2100XMM CVS 2 POLE 100 AMPS
Features	Eaton's main circuit breakers are used in a variety of applications including the main or emergency disconnect on the outside of a house, a tenant main breaker in group metering stacks and feed-through lug blocks specifically designed for sub-feeding from an existing panel. Main breakers are available with a variety of accessories including shunt trip, bell alarms and auxiliary switches.
Long Description	Eaton Type CV Molded Case Circuit Breaker, Molded case circuit breaker, 100 A, 42 kAIC, Two-pole, #6 - 4/0 Al/Cu, CV, #4/0 kcmil maximum load, Includes mounting kit
Product Type	CVS 2 Pole 100 Amps 42KA 240 Vac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685705880
Manufacturers Part Number	CVS2100XMM
UPC	786685705880

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Tenant main breaker

Packaging

Carton	1
Weight Per each	4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Datacenters - IT Space: CI and Hyper Converged
Renewable Energy - Alternative Energy
Energy - Conventional Energy
Equipment - Marine Vessels and Equipment - Other

standard

UL 489, CSA Std. C22.2 No. 5