

# Eaton CVS2125XMM

Catalog Number: CVS2125XMM

Eaton Type CV Molded Case Circuit Breaker, Molded case circuit breaker, 125 A, 42 kAIC, Two-pole, #6 - 4/0 Al/Cu, CV, #4/0 kcmil maximum load, Includes mounting kit



Photo is representative

## General specifications

|                               |                             |
|-------------------------------|-----------------------------|
| <b>Product Name</b>           | <b>Catalog Number</b>       |
| Eaton CCV tenant main breaker | CVS2125XMM                  |
| <b>UPC</b>                    | <b>Product Length/Depth</b> |
| 786685705897                  | 7.5 in                      |
| <b>Product Height</b>         | <b>Product Width</b>        |
| 5 in                          | 3.5 in                      |
| <b>Product Weight</b>         | <b>Warranty</b>             |
| 2.75 lb                       | Limited lifetime            |
| <b>Certifications</b>         |                             |
| UL 489                        |                             |
| CSA Std. C22.2 No. 5          |                             |

Type

Molded case circuit breaker

Amperage Rating

125 A

Circuit breaker frame type

CV

Accessories

Includes mounting kit

Terminals

#4/0 kcmil maximum load

Interrupt rating

42 kAIC

Wire size

#6-4/0 AWG Cu/Al

Number of poles

Two-pole

Brochures

Type CV Molded-case circuit breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CVS2125XMM



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia