



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D2488 Diagonal Cutting Pliers Angled Head Short Jaw, 8" *Klein Tools*

|                  |  |
|------------------|--|
| Catalog Number   | D2488  |
| Manufacturer     | Klein Tools  |
| Description      | Angled Diagonal Cutter, Steel Blade Material, 3/4 In Cutting Capacity, Plastic Dipped Steel Handle Material, Red (Handle), Plastic Dipped (Handle), 8-1/16 In Overall Length, 13/16 In Jaw Length, 1-3/16 In Jaw Width, 9.6 Oz |
| Weight per unit  | 0.6000 (lbs/each)  |
| Product Category | Pliers, Wrenches, Saw, Pouches   |

### Features

|                |                 |
|----------------|-----------------|
| Handle Length  | 6.75" (17.2 cm) |
| jaw thickness  | 0.46" (1.2 cm)  |
| Material       | Steel           |
| media          | Yes             |
| tether capable | No              |

### Material, Color, and Finish

|              |     |
|--------------|-----|
| Handle Color | Red |
|--------------|-----|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | DIAGONAL CUTTING PLIERS ANGLED HEAD SHORT JAW, 8" |
| extra long description | KLEIN D248-8 High Leverage Pliers,                |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00092644720703 |
| UPC  | 092644720703   |

### Taxonomies, Classifications, and Categories

|                      |                         |
|----------------------|-------------------------|
| Category Description | HAND TOOLS              |
| Type                 | Diagonal Cutting Pliers |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 6   |
| Weight Per each | 0.6 |

### Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | Non Ferrous Wire and Soft Metal Cutting |
|-------------|---|