

Eaton D2S20

Catalog Number: D2S20

Eaton Crouse-Hinds series D2S photocell, 50/60 Hz, Photocell in cover for use with FS/FD box, Used with LMV, DMV, VMV series luminaires, 120 Vac

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series D2S photocell	D2S20
	UPC
	782274901640
Product Length/Depth	Product Height
2.625 in	4.25 in
Product Width	Product Weight
2.19 in	0.57 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 2

Product specifications

Type

Photocell in cover for use with FS/FD box

Voltage rating

120 Vac

Frequency rating

50/60 Hz

Used with

LMV, DMV, VMV series luminaires

Resources

Catalogs

[Crouse-Hinds series Photocells catalog page](#)

Certification reports

[Photocells for Champ HID and Fluorescent Hazardous Area Light Fixtures](#)

[Canadian certification](#)

[Photocells for Champ HID and Fluorescent Hazardous Area Light Fixtures](#)

[UL certification](#)

Installation instructions

[IF 1293 - D2S Remote Photocell](#)

Specifications and datasheets

[Eaton Specification Sheet - D2S20](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)