

4-11/16" SQUARE (5S) BOXES

DRAWN


2-1/8" DEEP

42.0 Cu. In.


WITH RAISED GROUND EMBOSS & 10-32 GROUND SCREW




Cat. No.	Bracket & Setback	Knockouts		Std. Pkg.
		Sides	Bottom	
D5SDB-50/75	-	8 - 1/2", 4 - 3/4"	2 - 1/2", 2 - 3/4"	24
D5SDB-50/75-FB	FB, Flush	6 - 1/2", 3 - 3/4"	2 - 1/2", 2 - 3/4"	24
D5SDB-CKO	-	2 - 1/2", 10 - CKO	2 - 1/2", 2 - 3/4"	24
D5SDB-CKO-FB	FB, Flush	2 - 1/2", 7 - CKO	2 - 1/2", 2 - 3/4"	24
D5SDB-CKO-S	-	2 - 1/2", 10 - CKO	3 - 3/4"	24




D5SDB-50/75




D5SDB-50/75-FB



D5SDB-CKO



D5SDB-CKO-FB



D5SDB-CKO-S

4-11/16" SQUARE (5S) SUPER SHALLOW BOX & EXTENSION RING


WELDED

1-1/2" DEEP


29.5 Cu. In.

WITH RAISED GROUND EMBOSS (EXCEPT FOR EXTENSION RING)

Cat. No.	Knockouts		Std. Pkg.
	Sides	Bottom	
5SSB-MKO	8 - 1/2", 4 - MKO	2 - 1/2", 2 - MKO	24
5SSB-MKO-EXT	8 - 1/2", 4 - MKO	-	24



5SSB-MKO



5SSB-MKO-EXT

4-11/16" SQUARE (5S) LARGE CAPACITY BOXES

WELDED

2-1/2" DEEP

49.4 Cu. In.


WITH RAISED GROUND EMBOSS & TWO #8-32 x 1/2" MOUNTING SCREWS

Features:


- Suitable for Datacom & Electrical Applications



Cat. No.	Knockouts		Std. Pkg.
	Sides	Bottom	
5SLB-MKO	8 - 1/2", 4 - 1/2" & 3/4" M.K.O.	2 - 1/2", 2 - 3/4"	24
5SLB-2MKO	4 - 3/4" & 1" M.K.O., 4 - 1" & 1 - 1/4" M.K.O.	2 - 1/2", 2 - 3/4"	24



5SLB-MKO



5SLB-2MKO

- **600V** MKO's and CKO's suitable for bonding without any additional bonding means up to 600V
- Visit www.ul.com or QCIT Guide on page W1 for more information