



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DBYBULK Direct Bury Splice Kit

Minnesota Mining (3M)

Catalog Number	DBYBULK
Manufacturer	Minnesota Mining (3M)
Description	Splice Kit, Direct Burial; 30 V; Wire Combination Size (2 to 5) 18 Awg to (2) 12 Awg; Temperature Rating 32 to 120 Deg F; Connector Included; Contents (2) Tube, (2) Scotchlok[T] Y Connector; Standard Package Bulk; 3M[T] Brand; Dby Model
Weight per unit	0.0400 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Connector Included	YES
Contents	(2) TUBE, (2) SCOTCHLOK[T] Y CONNECTOR
Maximum Wire Combination Size	(2) 12 AWG
Minimum Wire Combination Size	(2 TO 5) 18 AWG
Voltage Rating	30 V

Descriptions

Commodity Description	SPLICING & TERMINATING KITS
Description	DIRECT BURY SPLICE KIT
extra long description	DIRECT BURIAL; 30 V VOLTAGE RATING; WIRE COMBINATION SIZE (2 TO 5) 18 AWG TO (2) 12 AWG; TEMPERATURE RATING 32 TO 120 DEG F; CONNECTOR INCLUDED; CONTENTS (100) TUBE, (100) CONNECTOR; STANDARD PACKAGE 100 PER CASE; DBY MODEL
Long Description	SPLICE KIT, DIRECT BURIAL; 30 V; WIRE COMBINATION SIZE (2 TO 5) 18 AWG TO (2) 12 AWG; TEMPERATURE RATING 32 TO 120 DEG F; CONNECTOR INCLUDED; CONTENTS (2) TUBE, (2) SCOTCHLOK[T] Y CONNECTOR; STANDARD PACKAGE BULK; 3M[T] BRAND; DBY MODEL
Product Type	Direct Bury Splice Kit

Manufacturer Information

Brand	Minnesota Mining (3M)
GTIN	00054007496984
Manufacturers Part Number	DBY-BULK
Model	DBY
UPC	054007496984

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	DIRECT BURIAL

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Standard Package	BULK
Weight Per each	0.04

Uses, Certifications, and Standards

Temperature Rating	32 TO 120 DEG F
--------------------	-----------------