

Eaton DC1-12011NB-A20CE1

Catalog Number: DC1-12011NB-A20CE1

Eaton DC-1 drive, IP20 240V 1PH IN/3PH OUT 3HP, 10.5A ENH FW

General specifications



Photo is representative

Product Name

Eaton PowerXL DC1 adjustable frequency drive

Catalog Number

DC1-12011NB-A20CE1

UPC

786687019282

Product Length/Depth

10.25 in

Product Height

9 in

Product Width

5.5 in

Product Weight

4.1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year cUL Certified from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first. Plus 5 years on capacitor cells.

Certifications

EN 61800-3
EN 60529
UL Listed
EN 61800-5-1

Line voltage

240V

Protection filtering

IP20

Type

VF drive

Number of inputs

1

Frame

2

Number of outputs

3

Rated operational current

10.5 A

Catalogs

[Product Datasheet - DC1-12011NB-A20CE1](#)

Specifications and datasheets

[Eaton Specification Sheet - DC1-12011NB-A20CE1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia