

# Eaton DC1-34024NB-A20CE1

Catalog Number: DC1-34024NB-A20CE1

DC1 IP20 480V IN/460V OUT 15HP, 24A ENH FW



## General specifications

|   |   |
|---|---|
| <b>Product Name</b>   | <b>Catalog Number</b>   |
| Eaton PowerXL DC1 adjustable frequency drive  | DC1-34024NB-A20CE1  |
|   | <b>UPC</b>  |
|   | 786687020240  |
| <b>Product Length/Depth</b>   | <b>Product Height</b>   |
| 13 in   | 9.75 in   |
| <b>Product Width</b>  | <b>Product Weight</b>   |
| 6.25 in   | 10 lb   |
| <b>Warranty</b>   | <b>Certifications</b>   |
| Eaton Selling Policy 25-000, one (1) year cUL Certified from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first. Plus 5 years on capacitor cells. | EN 61800-3<br>UkrSepro<br>EN 60529<br>UL Listed<br>EN 61800-5-1 |

defaultTaxonomyAttributeLabel

Resources

Type

VF drive

Frame

3

Rated operational current

24 A

Catalogs

[Product Datasheet - DC1-34024NB-A20CE1](#)

Specifications and datasheets

[Eaton Specification Sheet - DC1-34024NB-A20CE1](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)