



Powering Business Worldwide

pe.eaton.com

DC-1 Compact Frequency Inverter

DC1-342D2NN-A20N

UPC:786685858845

Dimensions:

- **Height:** 7.24 IN
- **Length:** 4.88 IN
- **Width:** 3.19 IN

Weight:2.43 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Display:** LED
- **Enclosure:** IP20 NEMA 0
- **Frame:** FS1
- **Horsepower:** 1 hp
- **Phase:** Three-phase mains/three-phase motor
- **Rated Operational Current:** 2.2A
- **Serial Interface:** Modbus
- **Type:** DC-1 Compact Frequency Inverter
- **User Interface:** RS-485
- **Voltage Rating:** 480V

Supporting documents:

- [Variable frequency drive - Product overview](#)
- [Datasheet](#)
- [DC1_A20N\(FR1\) 3D Model Xchange](#)
- [DC1_A20N\(FR1\) AutoCAD 2D Footprint](#)
- [DC1_A20N\(FR1\) 3D Inventor](#)
- [DC1_A20N\(FR1\) AutoCAD 2D Footprint \(mm\)](#)
- [DC1_A20N\(FR1\) 2D PDF](#)
- [DC1_A20N\(FR1\) 2D Drawing Xchange](#)



- [DC1 variable frequency drives](#)
- [DC1 compact variable frequency drives](#)
- [Eaton Specification Sheet - DC1-342D2NN-A20N](#)

Certifications:

- EN 60529
- UL Listed
- EN 61800-3
- UkrSepro
- cUL Certified
- EN 61800-5-1

Product compliance:

- CE Marked
- RoHS Compliant
- C-Tick Compliant



Powering Business Worldwide

pe.eaton.com

DC-1 Compact Frequency Inverter

DC1-342D2NN-A20N

UPC:786685858845

Dimensions:

- **Height:** 7.24 IN
- **Length:** 4.88 IN
- **Width:** 3.19 IN

Weight:2.43 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Display:** LED
- **Enclosure:** IP20 NEMA 0
- **Frame:** FS1
- **Horsepower:** 1 hp
- **Phase:** Three-phase mains/three-phase motor
- **Rated Operational Current:** 2.2A
- **Serial Interface:** Modbus
- **Type:** DC-1 Compact Frequency Inverter
- **User Interface:** RS-485
- **Voltage Rating:** 480V

Supporting documents:

- [Variable frequency drive - Product overview](#)
- [Datasheet](#)
- [DC1_A20N\(FR1\) 3D Model Xchange](#)
- [DC1_A20N\(FR1\) AutoCAD 2D Footprint](#)
- [DC1_A20N\(FR1\) 3D Inventor](#)
- [DC1_A20N\(FR1\) AutoCAD 2D Footprint \(mm\)](#)
- [DC1_A20N\(FR1\) 2D PDF](#)
- [DC1_A20N\(FR1\) 2D Drawing Xchange](#)



- [DC1 variable frequency drives](#)
- [DC1 compact variable frequency drives](#)
- [Eaton Specification Sheet - DC1-342D2NN-A20N](#)

Certifications:

- EN 60529
- UL Listed
- EN 61800-3
- UkrSepro
- cUL Certified
- EN 61800-5-1

Product compliance:

- CE Marked
- RoHS Compliant
- C-Tick Compliant