



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DE1127D0N NN20N DE1 1PH 230V In 3PH 230V Out 7.0A 2HP

Eaton Corp

Catalog Number	DE1127D0N NN20N
Manufacturer	Eaton Corp
Description	Eaton DE1 Variable Speed Starter Modbus IP20 230V Single-Phase Mains Connection/Three-Phase Motor Connection 7.0A 2HP FS1
Weight per unit	3.4 (lbs/each)
Product Category	20150313150910

Features

dimensions	9.0900 IN X 6.6500 IN X 1.7700 IN
------------	-----------------------------------

Descriptions

Description	DE1 1PH 230V IN 3PH 230V OUT 7.0A 2HP
extra long description	ETN DE1-127D0NN-N20N DE1 1PH 230V I
Features	With 14 basic parameters, SmartWire-DT connectivity, and an intuitive configuration module, the PowerXL DE1 variable speed starter set up and commissioning is easy for any panel builder and MOEM. The DE1 was designed for customers who have basic application but still require variable frequency and advanced motor protection. The design allows customers to simplify their design and reduce installation and commissioning time while introducing an innovative solution to their system.

Long Description	Eaton DE1 Variable Speed Starter Modbus IP20 230V SINGLE-phase mains connection/three-phase motor connection 7.0A 2Hp FS1
------------------	---

Product Type	DE1 1PH 230V In, 3PH 230V Out, 7.0A, 2HP
--------------	--

Manufacturer Information

Brand	Eaton
GTIN	00786685949024
Manufacturers Part Number	DE1-127D0NN-N20N
UPC	786685949024

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable speed starter

Packaging

Carton	1
Weight Per each	3.43



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other

standard

C-Tick Compliant, CE Marked, RoHS Compliant