

Eaton DE1-127D0NN-N20N

Catalog Number: DE1-127D0NN-N20N

Eaton DE1 Variable Speed Starter Modbus IP20 230V SINGLE-phase mains connection/three-phase motor connection 7.0A 2Hp FS1



Photo is representative

General specifications

Product Name	Catalog Number
Eaton PowerXL DE1 variable speed starter	DE1-127D0NN-N20N
	UPC
	786685949024
Product Length/Depth	Product Height
9.09 in	1.77 in
Product Width	Product Weight
6.65 in	2.29 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	RoHS Compliant

Serial interface

Modbus

User interface

RS-485

Display

None

Enclosure

IP20

Frame

2

Catalogs

Product Datasheet - DE1-127D0NN-N20N

Drawings

DE1_(FR1) AutoCAD 2D Footprint

DE1_(FR1) 2D PDF

DE1_(FR1) AutoCAD 2D Footprint (mm)

DE1_(FR1) 3D Inventor

DE1_(FR1) 3D Model Xchange

DE1_(FR1) 2D Drawing Xchange

Specifications and datasheets

Eaton Specification Sheet - DE1-127D0NN-N20N

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia