

DURAFLOOD SPEC 50

50W LED FLOOD LIGHT
150W MH REPLACEMENT



Lumens	6,000
LED Source	Lumileds 3030
Driver	Mean Well
CCT	3000K, 5000K
CRI	> 80
Beam Angle	120°
Operating Voltage	100 - 277 VAC, 50/60 HZ
Power Consumption	50W
Lifespan	> 50,000 Hours
IP Grade	IP65
Body Construction	Aluminum and Tempered Glass
Dimensions	9.4" x 6.3" x 3.1"
Weight	5.7 lbs

ORDER CODE Example **DFS50Y-BRZ-120D5KA-2V**

Fixture	Mount	Housing	Beam Angle	CCT	Voltage
DFS50	K - Knuckle	BRZ - Bronze	120D - 120°	3K - 3000K	A-2V - 100-277 VAC
	T - Trunnion			5K - 5000K	A-4V - 277-480 VAC
	Y - Yoke				