



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG132017FBC21C DG1 230V FR2 N1 5HP 17.5A CT 7.5HP 25A VT W/ BC Eaton Corp

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | DG132017FBC21C |
| Manufacturer | Eaton Corp |
| Description | Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input 3.7 KW 5 HP CT 3PH 50/60 HZ 17.5A Output IP21/Type 1 FR2 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots Brake Chopper |
| Weight per unit | 29.0 (lbs/each) |
| Product Category | Ac Drives |

Features

| | |
|---------------|------------------------------|
| display | LCD graphical |
| Input Voltage | 230 V, 208-240 V(-15%, +10%) |
| keypad | Included |

Dimensions and Weight

| | |
|--------|----|
| Depth | 21 |
| Height | 15 |
| Width | 10 |

Descriptions

| | |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | DG1 230V FR2 N1 5HP 17.5A CT 7.5HP 25A VT W/ BC |
| extra long description | ETN DG1-32017FB-C21C DG1,230V FR2,N |
| Features | Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability. |
| Long Description | Eaton PowerXL DG1 variable frequency drive, 208-240V input 3.7 kW 5 Hp CT 3PH 50/60 Hz 17.5A output IP21/type 1 FR2 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots Brake chopper |
| Product Type | DG1, 230V FR2, N1, 5HP, 17.5A/7.5HP, 25A, BC |
| Special Features | Coated board |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Eaton |
| GTIN | 00786685886060 |
| Manufacturers Part Number | DG1-32017FB-C21C |
| UPC | 786685886060 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DRIVES

Type Variable Frequency Drive

Packaging

Carton 1

Weight Per each 29

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

Enclosure IP21/type 1 enclosure

standard EN ISO 13849-1,EN 62061,cUL Listed,IEC 61508,UL Listed,UL
508C,CE Marked,RoHS Compliant,GoST-R,C-Tick Compliant