



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG132048FBC21C DG1 230V FR3 N1 15HP 48A CT 20HP 61A VT W/ BC Eaton Corp

Catalog Number	DG132048FBC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input 11 KW 15 HP CT 3PH 50/60 HZ 48A Output IP21/Type 1 Enclosure FR3 LCD Display Internal Emc Filter and DC Choke Ethernet
Weight per unit	53.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	230 V, 208-240 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	27
Height	16
Width	11.5

Descriptions

Description	DG1 230V FR3 N1 15HP 48A CT 20HP 61A VT W/ BC
extra long description	ETN DG1-32048FB-C21C DG1,230V FR3,N
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 208-240V input 11 kW 15 Hp CT 3PH 50/60 Hz 48A output IP21/type 1 enclosure FR3 LCD display Internal EMC filter and DC choke EtherNet
Product Type	DG1, 230V FR3, N1, 15HP, 48A/20HP, 61A, BC
Special Features	Coated board

Manufacturer Information

Brand	Eaton
GTIN	00786685886091
Manufacturers Part Number	DG1-32048FB-C21C
UPC	786685886091

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	53

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	IP21/type 1 enclosure EN ISO 13849-1, IEC 61508, cUL Listed, UL Listed, UL 508C, EN 62061, C-Tick Compliant, CE Marked, RoHS Compliant, GoST-R