



Powering Business Worldwide

pe.eaton.com

General Duty Cartridge Fuse Safety Switch

DG225NRK

UPC:782113589503

Dimensions:

- **Height:** 44.31 IN
- **Length:** 11.16 IN
- **Width:** 22.66 IN

Weight:112 LB

Notes:Maximum hp ratings apply only when dual element fuses are used. 3-Phase hp rating shown is a grounded B phase rating, UL listed.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** General Duty/Cartridge Fuse
- **Amperage Rating:** 400A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG225NRK](#)

Certifications:

- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

General Duty Cartridge Fuse Safety Switch

DG225NRK

UPC:782113589503

Dimensions:

- **Height:** 44.31 IN
- **Length:** 11.16 IN
- **Width:** 22.66 IN

Weight:112 LB

Notes:Maximum hp ratings apply only when dual element fuses are used. 3-Phase hp rating shown is a grounded B phase rating, UL listed.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** General Duty/Cartridge Fuse
- **Amperage Rating:** 400A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG225NRK](#)

Certifications:

- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.