



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General Duty Non-Fusible Safety Switch

**DG323UGB**

**UPC:**782113144368

### Dimensions:

- **Height:** 7.5 IN
- **Length:** 6.42 IN
- **Width:** 8.82 IN

**Weight:**9 LB

**Notes:**WARNING! Switch is not approved for service entrance unless a neutral kit is installed.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** General Duty/Non-Fusible
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Fuse Configuration:** Non-fusible
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG323UGB](#)

### Certifications:

- UL Listed

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General Duty Non-Fusible Safety Switch

**DG323UGB**

**UPC:**782113144368

### Dimensions:

- **Height:** 7.5 IN
- **Length:** 6.42 IN
- **Width:** 8.82 IN

**Weight:**9 LB

**Notes:**WARNING! Switch is not approved for service entrance unless a neutral kit is installed.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** General Duty/Non-Fusible
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Fuse Configuration:** Non-fusible
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG323UGB](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



