

Eaton DH221FGK

Catalog Number: DH221FGK

Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 30 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Two-pole, Two-wire, 240 V, Max Hp: 1.5, 5 hp (1PH @240V/250 Vdc), #14-#2 Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH221FGK
UPC	Product Length/Depth
782114370322	18 in
Product Height	Product Width
7.5 in	9.5 in
Product Weight	Warranty
14 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
NEC 230.62 (C) Compliant Barrier	UL Listed
Catalog Notes	
Suitable for service entrance use with a neutral or ground lug kit installed	

Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Two-pole

Number of wires

2

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

30A

HP rating - max

1.5, 5 hp (1PH @240V/250 Vdc)

NEMA rating

NEMA 1

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH221FGK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)