# Eaton DH221NRK

# Catalog Number: DH221NRK

Eaton enhanced visible blade single-throw fused safety switch, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible with neutral, Two-pole, Three-wire, 240 V, Max Hp: 1.5, 3 hp/3, 7.5 hp/5 hp (1,3PH @ Std fuse/time delay/250 Vdc)

## General specifications



Product Name Catalog Number
Eaton heavy duty fusible safety switch DH221NRK

UPC Product Length/Depth

782113205359 16.5 in

Product Height Product Width

8.31 in 9.12 in

Product Weight Warranty

13.6 lb Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications Catalog Notes

UL Listed 3-Phase hp ratings shown are grounded

CSA Certified B phase ratings; UL listed



## **Physical Attributes**

Enclosure

NEMA 3R

**Enclosure material** 

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

**Number Of Poles** 

Two-pole

Number of wires

3

Type

Heavy duty fusible safety switch

#### Performance Ratings

**Amperage Rating** 

30A

HP rating - max

1.5, 3 hp/3, 7.5 hp/5 hp (1,3PH @ Std fuse/time delay/250 Vdc)

**NEMA** rating

NEMA 3R

Voltage rating

240V

#### Miscellaneous

#### **Product Category**

Heavy Duty, Fusible with neutral

#### Resources

#### Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH221NRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia