



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH262FRK 60A/2P HD Fusible Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH262FRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 60 A, Nema 3R, Painted Galvanized Steel, Class H, Fusible Without Neutral, Two-Pole, Two-Wire, 600 V, Max HP: 20, 25 HP/25 HP (1PH @480, 600 V TD/600 VDC), #14-#2 Cu/Al
Weight per unit	20.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	60
Material	Galvanized Steel
media	Yes
Poles	2
Voltage Rating	600 V

### Dimensions and Weight

Depth	17
Height	16.27
Width	9.5

### Descriptions

Description	60A/2P HD FUSIBLE SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH262FRK 60A/2P HD Fusible Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 60 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Two-pole, Two-wire, 600 V, Max Hp: 20, 25 hp/25 hp (1PH @480,600 V TD/600 Vdc), #14-#2 Cu/Al
Product Type	60A/2P HD Fusible Sfty SW 600V N3R

### Manufacturer Information

Brand	Eaton
GTIN	00786685177137
Manufacturers Part Number	DH262FRK
UPC	786685177137

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	20

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed