

Eaton DH362FDK

Catalog Number: DH362FDK

Eaton Heavy duty receptacle safety switch, 60 A, NEMA 12/3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 20, 25/ 30, 50 hp (1/3PH @480, 600 V), #14-#2 Cu/Al

General specifications



Product Name

Eaton heavy duty fusible safety switch

Catalog Number

DH362FDK

UPC

782113206141

Product Length/Depth

20 in

Product Height

8.5 in

Product Width

9.5 in

Product Weight

22 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Suitable for service entrance use with a neutral or ground lug kit installed. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty fusible safety switch

Wire size

#14-2 AWG Cu/Al

Performance Ratings

Amperage Rating

60A

HP rating - max

20, 25/ 30, 50 hp (1/3PH @480, 600 V)

NEMA rating

NEMA 12/3R

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

Resources

Brochures

[Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Drawings

[30and60A 3POLE FUSIBLE T12](#)

Specifications and datasheets

[Eaton Specification Sheet - DH362FDK](#)