



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DIOD224V96W 24V 96W Omnidrive Dimmable Driver

Diode Led

Catalog Number	DIOD224V96W
Manufacturer	Diode Led
Description	24V 96W Omnidrive 2 Electronic Dimmable Driver
Weight per unit	4.0 (lbs/each)
Product Category	Lighting

Features

Category	Specialty Items
----------	-----------------

Material, Color, and Finish

Finish	BLACK GLOSS
Style	Transitional

Descriptions

Description	24V 96W OMNIDRIVE DIMMABLE DRIVER
extra long description	ELECTRONIC DIMMABLE LED DRIVER, FANLESS TYPE; OMNIDRIVE[R] BRAND; ROHS COMPLIANT; CONNECTION TYPE SCREW TERMINAL; VOLTAGE RATING 24 VOLT DC (OUTPUT); CURRENT RATING 4 AMP (MAXIMUM LOAD), 1.9 AMP (FULL LOAD); POWER RATING 96 WATT; HOUSING TYPE BLACK POWDER COATED STEEL ENCLOSURE; TEMPERATURE RATING -40 TO 176 DEG F; RELATIVE HUMIDITY 20 TO 90 PERCENT NON-CONDENSING; APPLICATION INDOOR, DRY LOCATION; OVERALL DIMENSION 15 INCH LENGTH X 3.1 INCH WIDTH X 2.4 INCH HEIGHT; APPLICABLE STANDARD UL, CSA, ETL, FCC
Long Description	24V 96W OMNIDRIVE 2 ELECTRONIC DIMMABLE DRIVER
Product Type	Electronic Dimmable Driver

Manufacturer Information

Brand	Diode Led
GTIN	00848333011672
Manufacturers Part Number	DI-OD2-24V96W
UPC	848333011672

Taxonomies, Classifications, and Categories

Type	Fixture Accents/Parts
------	-----------------------

Packaging

Carton	1
Weight Per each	4