

# Eaton DI10P-W

Catalog Number: DI10P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 1000W 662447



## General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DI10P-W
UPC	Product Length/Depth
032664662447	2.063 in
Product Height	Product Width
4.375 in	3.125 in
Product Weight	Certifications
0.001 lb	cULus Listed NOM

## Product specifications

### Special features

Preset feature

### Switch type

Single-pole, three-way

### Load type

HAL

MLV

INC

### Color

White

### Wiring method

Back and side

### Material

Polycarbonate

### Housing

Polycarbonate

### Type

Dimmer

### Power consumption

1000 W

### Environmental conditions

Indoor

### Frequency rating

60 Hz

### Connection type

Wire lead

### Voltage rating

120 V

### Torque rating

14 lbf-inch

### Actuator

Slide

## Resources

### Brochures

[Lighting controls line card brochure](#)

### Installation videos

[How to install Eaton's universal slide dimmers](#)

### Specifications and datasheets

[Eaton Specification Sheet - DI10P-W](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)