

# DLS

4"



5 5/8"



## TECHNICAL SPECIFICATIONS:

- ⌘ Construction: Spun aluminum
- ⌘ LED: Unique enclosed DOB (Driver On Board) LED board enclosed in clear plastic casing for better damp location performance
- ⌘ Gasket: close cell Neoprene foam gasket
- ⌘ Lens: White translucent acrylic
- ⌘ Isolated driver for improved thermal management
- ⌘ CRI: 90
- ⌘ Working Voltage: 120V AC
- ⌘ Dimmable
- ⌘ LED: Seoul DOB (Driver On Board) Technology
- ⌘ Power factor: 90% +
- ⌘ Suitable for damp locations
- ⌘ Maximum Ambient Temperature: 104°F
- ⌘ Energy Star-rated
- ⌘ Fit on recessed housings / Fit on standard 4" octagonal (40) or 3" octagonal (30) electrical boxes



## ACCESSORIES INCLUDED



for DLS4



for DLS6

## LED DISK LIGHTS—4" & 5" / 6" ROUND

| CATALOG NO. | FINISH         | WATTS | COLOR TEMP | LUMENS     | DIAMETER |
|-------------|----------------|-------|------------|------------|----------|
| DLS4-27K    | WHITE          | 9W    | 2700K      | 550~600LM  | 4"       |
| DLS4-30K    | WHITE          | 9W    | 3000K      | 550~600LM  |          |
| DLS4-41K    | WHITE          | 9W    | 4000K      | 550~600LM  |          |
| DLS4-50K    | WHITE          | 9W    | 5000K      | 550~600LM  |          |
| DLS6-27K    | WHITE          | 15W   | 2700K      | 950~1000LM | 5" / 6"  |
| DLS6-30K    | WHITE          | 15W   | 3000K      | 950~1000LM |          |
| DLS6-41K    | WHITE          | 15W   | 4000K      | 950~1000LM |          |
| DLS6-50K    | WHITE          | 15W   | 5000K      | 950~1000LM |          |
| DLS6-30K-BR | BRONZE         | 15W   | 3000K      | 950~1000LM |          |
| DLS6-30K-BN | BRUSHED NICKEL | 15W   | 3000K      | 950~1000LM |          |



# DLS

4"



5 5/8"



## TECHNICAL SPECIFICATIONS:

- :: Construction: Spun aluminum
- :: LED: Unique enclosed DOB (Driver On Board) LED board enclosed in clear plastic casing for better damp location performance
- :: Gasket: close cell Neoprene foam gasket
- :: Lens: White translucent acrylic
- :: Isolated driver for improved thermal management
- :: CRI: 90
- :: Working Voltage: 120V AC
- :: Dimmable
- :: LED: Seoul DOB (Driver On Board) Technology
- :: Power factor: 90% +
- :: Suitable for damp locations
- :: Maximum Ambient Temperature: 104°F
- :: Energy Star-rated
- :: Fit on recessed housings / Fit on standard 4" octagonal (40) or 3" octagonal (30) electrical boxes



## ACCESSORIES INCLUDED



for DLS4



for DLS6

## LED DISK LIGHTS—4" & 5" / 6" ROUND

| CATALOG NO. | FINISH         | WATTS | COLOR TEMP | LUMENS     | DIAMETER |
|-------------|----------------|-------|------------|------------|----------|
| DLS4-27K    | WHITE          | 9W    | 2700K      | 550~600LM  | 4"       |
| DLS4-30K    | WHITE          | 9W    | 3000K      | 550~600LM  |          |
| DLS4-41K    | WHITE          | 9W    | 4000K      | 550~600LM  |          |
| DLS4-50K    | WHITE          | 9W    | 5000K      | 550~600LM  |          |
| DLS6-27K    | WHITE          | 15W   | 2700K      | 950~1000LM | 5" / 6"  |
| DLS6-30K    | WHITE          | 15W   | 3000K      | 950~1000LM |          |
| DLS6-41K    | WHITE          | 15W   | 4000K      | 950~1000LM |          |
| DLS6-50K    | WHITE          | 15W   | 5000K      | 950~1000LM |          |
| DLS6-30K-BR | BRONZE         | 15W   | 3000K      | 950~1000LM |          |
| DLS6-30K-BN | BRUSHED NICKEL | 15W   | 3000K      | 950~1000LM |          |

