

Eaton DMM-B-44/100

Catalog Number: DMM-B-44/100

Eaton Bussmann series DMM-B fuse, Fast acting fuse, Multimeters only, 0.44 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 1000 Vac/dc, Standard, 1000 V, 1000 Vdc

General specifications



| | |
|----------------------------------|----------------|
| Product Name | Catalog Number |
| Eaton Bussmann series DMM-B fuse | DMM-B-44/100 |
| UPC | EAN |
| 051712550550 | 5027590059572 |
| Product Length/Depth | Product Height |
| 0.46 in | 1.5 in |
| Product Width | Product Weight |
| 0.46 in | 0.15 lb |
| Warranty | Compliances |
| Not Applicable | CE Marked |

Product specifications

Fuse indicator

Non-indicating

Special features

Non current limiting

Interrupt rating

10 kAIC at 1000 Vac/dc

Type

Fast acting fuse

Connection

Ferrule end x ferrule end

Voltage rating

1000 Vac, 1000 Vdc

Application

Multimeters only

Amperage Rating

0.44A

Packaging type

Standard

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Specifications and datasheets

Eaton Specification Sheet - DMM-B-44/100

Technical data sheets

Bussmann series DMM digital multi-meter fuse data sheet No.1047

DMM-B-44/100~DMM-B-44-100~DMM FUSE - BUSSMANN



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia