



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DMW232MVOLTGEB10 Wet Location Fluorescent 2LMP 32W

Lithonia Lighting

Catalog Number	DMW232MVOLTGEB10
Manufacturer	Lithonia Lighting
Description	The Lithonia Lighting® 4-Foot, 2-Light White T8 Fluorescent Enclosed and Gasketed Strip Light By Lithonia Lighting Is Ideal Where Dirt, Dust, Humidity and Moisture Are Present
Weight per unit	12.1 (lbs/each)
Product Category	Fluorescent Wet Location Light

Features

average life	40,000
Ballast Type	Electronic Ballast
Fixture Type	Linear
fixture wattage	64 W
Hardware	Yes
Housing Finish	Gloss
Lamp Type	Fluorescent
Lamp Wattage	32
Material	Fiberglass
Number of Lamps	2
pallet quantity	41
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	1
Wattage	64.0000000000000000

Material, Color, and Finish

Color	Beige
housing color	Beige
Housing Material	Fiberglass
Lens Color	WHITE
Lens Material	Acrylic

Dimensions and Weight

Height	5.5
Length	50
Width	9.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WET LOCATION FLOURESCENT 2LMP 32W
extra long description	LITH DMW 2 32 MVOLT GEB10IS Enclose
Long Description	The Lithonia Lighting® 4-foot, 2-light white T8 fluorescent enclosed and gasketed strip light by Lithonia Lighting is ideal where dirt, dust, humidity and moisture are present
Product Type	Linear

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00784231151099
Manufacturers Part Number	DMW 2 32 MVOLT GEB10IS
UPC	784231151099

Taxonomies, Classifications, and Categories

Category Description	Flourescent Fixtures & Accessories
Type	LINEAR

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight	12
Weight Per each	12.1

Uses, Certifications, and Standards

Application	Automotive & Parking,Education,Enclosed & Gasketed,Government,Healthcare,Hospitality,House of Worship,Manufacturing,Offices & Banks,Power & Gas,Retail,Special Applications,Sports and Recreation,Transportation,Warehouses
environmental conditions	Demanding,Indoor
Mounting	Surface,Suspended
standard	CSA,UL