# Eaton DPB222R

## Catalog Number: DPB222R

Eaton Air Conditioning Disconnect, Molded case switch, 60 A, 240V, 10 kAIC, #14-3 Cu/AI 60°C or 75°C, NEMA 3R Galvanized Steel enclosure, 10 hp at 240V, ANSI 61 gray

#### General specifications

**Product Name** 

Catalog Number

Eaton air conditioning disconnect

DPB222R

UPC

Product Length/Depth

782114205686

5.3 in

**Product Height** 

Product Width

8.6 in

3.74 in

**Product Weight** 

Warranty

3.11 lb

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications

Catalog Notes

UL Listed

For replacement molded case switch,

CSA Certified

order part number BR260NA.



### default Taxonomy Attribute Label

Type

Air conditioning disconnect

**Amperage Rating** 

60A

Horsepower

10 hp at 240 V

Voltage rating

240V

Wire size

#14-3 AWG Cu/AI

Color

ANSI 61 gray

**Enclosure** 

NEMA 3R

**Enclosure material** 

Galvanized steel

Interrupt rating

10 kAIC

#### Resources

**Brochures** 

Air Conditioning Disconnects

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - DPB222R



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia