



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Air Conditioning Disconnect

**DPU222RGF20ST**

**UPC:**786685982182

**Dimensions:**

- **Height:** 13 IN
- **Length:** 7.5 IN
- **Width:** 4.75 IN

**Weight:**8 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** Non-fused pullout
- **Amperage Rating:** 60A
- **Color:** ANSI 61 gray
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Galvanized steel
- **Interrupt Rating:** 10 kAIC
- **Receptacle:** 20A ground fault self-test receptacle
- **Voltage Rating:** 120/240V
- **Wire Size:** #14-3 AWG Cu/Al

**Supporting documents:**

- [Eaton Specification Sheet - DPU222RGF20ST](#)

**Certifications:** No Data

**Product compliance:** No Data





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Air Conditioning Disconnect

**DPU222RGF20ST**

**UPC:**786685982182

**Dimensions:**

- **Height:** 13 IN
- **Length:** 7.5 IN
- **Width:** 4.75 IN

**Weight:**8 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** Non-fused pullout
- **Amperage Rating:** 60A
- **Color:** ANSI 61 gray
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Galvanized steel
- **Interrupt Rating:** 10 kAIC
- **Receptacle:** 20A ground fault self-test receptacle
- **Voltage Rating:** 120/240V
- **Wire Size:** #14-3 AWG Cu/Al

**Supporting documents:**

- [Eaton Specification Sheet - DPU222RGF20ST](#)

**Certifications:** No Data

**Product compliance:** No Data

