

# Eaton DS161R

Catalog Number: DS161R

Eaton Type DS disconnect switch, Panel Mounted Disconnects, Type DS - Disconnect Switch, 30A, 600 Vac, 250 Vdc, Three-pole, Three-wire, Fusible, Complete unit, Class R fuses, 30A at 600 Vac fuse clips, 30A switch rating, NEC 600 type volts

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type DS disconnect switch	DS161R
<b>UPC</b>	<b>Product Length/Depth</b>
662276610651	9.9 in
<b>Product Height</b>	<b>Product Width</b>
5.3 in	6 in
<b>Product Weight</b>	<b>Certifications</b>
3.15 lb	UL Listed CSA Certified

## Catalog Notes

Terminals are suitable for either copper or aluminum cable. Suitable for Class J fuses. UL listed for use with Class R fuses when fuse clip conversion kits are used.

defaultTaxonomyAttributeLabel

Resources

### Amperage Rating

30A

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Multimedia

[Single-phase disconnect and bypass switches](#)

### Specifications and datasheets

[Eaton Specification Sheet - DS161R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)