

Eaton DSD917

Catalog Number: DSD917

Eaton Crouse-Hinds series DSD manual motor starter cover and device sub-assembly, 20A/30A, 3-pole, 7.5 HP/15 HP, Arrow Hart, Feraloy iron alloy, 250/600 Vac

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series DSD manual motor starter cover and device sub-assembly	DSD917
	UPC
	782274575773
Product Length/Depth	Product Height
5 in	3.5 in
Product Width	Product Weight
3.5 in	2.45 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

Product specifications

Manufacturer

Arrow Hart

Number Of Poles

Three-pole

Horsepower

7.50 hp, 15 hp

Voltage rating

250 Vac /600 Vac

Configuration

3-pole

Amperage Rating

20A/30A

Material

Feraloy iron alloy

Resources

Catalogs

[DSD and DSDX Cover and Device Sub-assemblies catalog page](#)

Certification reports

[DSD Explosionproof Cover and Device Sub-assemblies UL certification](#)

[DSD Explosionproof Cover and Device Sub-assemblies Canadian certification](#)

Installation instructions

[IF 1424 - DSD, GFS, CPS and ENR Series Replacement Covers](#)

[IF 1929 - Toggle Operator for EDS, EDSX, EFD, DSD and DSDX Series](#)

[IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations](#)

Specifications and datasheets

[Eaton Specification Sheet - DSD917](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)