

Eaton DSD918 S769

Catalog Number: DSD918 S769

Eaton Crouse-Hinds series DSD front operated pushbutton cover and device sub-assembly, 10A, Red, Feraloy iron alloy, 1 circuit universal, 1 button, Maintained red emergency "STOP" button with lockout, factory sealed, 600 Vac



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series DSD front operated pushbutton cover and device sub-assembly	DSD918 S769
	UPC
	782274020976
Product Length/Depth	Product Height
5.25 in	3.5 in
Product Width	Product Weight
5 in	3.8 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

Product specifications

Voltage rating

600 Vac

Number of cover buttons

1

Normal position

1 circuit universal

Amperage Rating

10A

Color

Red

Material

Feraloy iron alloy

Special features

Maintained red emergency "STOP" button with lockout, factory sealed

Resources

Catalogs

[DSD and DSDX Cover and Device Sub-assemblies catalog page](#)

Certification reports

[DSD Explosionproof Cover and Device Sub-assemblies Canadian certification](#)

[DSD Explosionproof Cover and Device Sub-assemblies UL certification](#)

Installation instructions

[IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations](#)

[IF 1929 - Toggle Operator for EDS, EDSX, EFD, DSD and DSDX Series](#)

[IF 1424 - DSD, GFS, CPS and ENR Series Replacement Covers](#)

Specifications and datasheets

[Eaton Specification Sheet - DSD918 S769](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)