



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DV10250D #10 VNL F Disc Panduit Corporation

Catalog Number	DV10250D
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Female Disconnect Is Made Of Brass and Is Tin-Plated. It Is Barrel Insulated In Yellow Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 12-10 Awg (4.0-6.0 MM ²). It Is 1.03" (26.2 MM) Long and 0.3" (7.6 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Sleaved Barrel. It Comes In Boxes Of 500.
Weight per unit	0.0041 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Brass
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Descriptions

Description	#10 VNL F DISC
extra long description	PAN DV10-250-D Pan-Term® DV10-250-D
Long Description	The vibration resistant female disconnect is made of brass and is tin-plated. It is barrel insulated in yellow vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 12-10 AWG (4.0-6.0 mm ²). It is 1.03" (26.2 mm) long and 0.3" (7.6 mm) wide. The disconnect has a funnel entry barrel configuration and a sleaved barrel. It comes in boxes of 500.
Product Type	Pan-Term® DV10-250-D Disconnect, Yellow, Vinyl, 10-12 Awg, 0

Manufacturer Information

Brand	PANDUIT
GTIN	00074983821051
Manufacturers Part Number	DV10-250-D
UPC	074983821051

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	3000
Package	500
Weight Per each	0.0041

Uses, Certifications, and Standards

Mounting	1932-09-01
standard	CSA Certified LR31212, C22.2 No.153;UL 310 Listed, UL Listed 20H3 E78522
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)