



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVSTVWH Diva DV 8A 0-10V 3WAY White Lutron

Catalog Number	DVSTVWH
Manufacturer	Lutron
Description	Dimmable Bulb, Paddle Switch, 120 to 277 V, 3 W, Fluorescent Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.26 LB/Ea
Weight per unit	0.2600 (lbs/each)
Product Category	Lighting Dimmers

Features

amperage rating	8
Connection Type	Wire Leads
insulation	Plastic
media	Yes
Poles	1
Wattage	2216

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

Descriptions

Description	DIVA DV 8A 0-10V 3WAY WHITE
extra long description	LUT DVSTV-WH DIVA 0-10 W/SWITCHING
Special Features	Controls 0-10 V LED or fluorescent fixture loads, 50 mA max control current. Paddle turns on/off. Slide up to brighten, down to dim.

Manufacturer Information

GTIN	00784276099622
UPC	784276099622

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, 3-way/single-pole

Packaging

Carton	1
Package	4
Weight Per each	0.26



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
standard	UL, CSA